

# Eaton TP574

Catalog Number: TP574

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, one device, Steel, 1/4" raised, 1.8 cubic inch capacity



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square cover	TP574
UPC	Product Length/Depth
786189105742	4.69 in
Product Height	Product Width
0.25 in	4.69 in
Product Weight	
0.32 lb	

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4-11/16"

### Capacity

1.8 cubic in

### Color

Natural

### Configuration

Raised surface, one device

### Material

Steel

### Type

1/4" raised

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds TP574 3D drawing](#)

### Catalogs

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP574](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP574

Catalog Number: TP574

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, one device, Steel, 1/4" raised, 1.8 cubic inch capacity



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square cover	TP574
UPC	Product Length/Depth
786189105742	4.69 in
Product Height	Product Width
0.25 in	4.69 in
Product Weight	
0.32 lb	

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4-11/16"

### Capacity

1.8 cubic in

### Color

Natural

### Configuration

Raised surface, one device

### Material

Steel

### Type

1/4" raised

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds TP574 3D drawing](#)

### Catalogs

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP574](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)