

Eaton TP587

Catalog Number: TP587

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, two device, Steel, 5/8" raised, 8.0 cubic inch capacity



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square cover	TP587
UPC	Product Length/Depth
786189105872	4.69 in
Product Height	Product Width
0.63 in	4.69 in
Product Weight	
0.32 lb	

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4-11/16"

Capacity

8 cubic in

Color

Natural

Configuration

Raised surface, two device

Material

Steel

Type

5/8" raised

Resources

3D CAD drawing package

[Eaton Crouse-Hinds TP587 3D drawing](#)

Catalogs

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

Certification reports

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP587](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP587

Catalog Number: TP587

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, two device, Steel, 5/8" raised, 8.0 cubic inch capacity



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square cover	TP587
UPC	Product Length/Depth
786189105872	4.69 in
Product Height	Product Width
0.63 in	4.69 in
Product Weight	
0.32 lb	

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4-11/16"

Capacity

8 cubic in

Color

Natural

Configuration

Raised surface, two device

Material

Steel

Type

5/8" raised

Resources

3D CAD drawing package

[Eaton Crouse-Hinds TP587 3D drawing](#)

Catalogs

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

Certification reports

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP587](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)