

Specifications



Photo is representative

Eaton TP586

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, two device, Steel, 3/4" raised, 8.8 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square cover
CATALOG NUMBER	TP586
UPC	786189105865
PRODUCT LENGTH/DEPTH	4.69 in
PRODUCT HEIGHT	0.75 in
PRODUCT WIDTH	4.69 in
PRODUCT WEIGHT	0.34 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
---------------------	------------------------

Product specifications

BOX SIZE	4-11/16"
----------	----------

	Locations
STANDARDS TYPE	NEC/CEC

CAPACITY	8.8 cubic in
COLOR	Natural
CONFIGURATION	Raised surface, two device
MATERIAL	Steel
TYPE	3/4" raised

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP586 3D drawing](#)

CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP586](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

Reserved.



Specifications



Photo is representative

Eaton TP586

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, two device, Steel, 3/4" raised, 8.8 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square cover
CATALOG NUMBER	TP586
UPC	786189105865
PRODUCT LENGTH/DEPTH	4.69 in
PRODUCT HEIGHT	0.75 in
PRODUCT WIDTH	4.69 in
PRODUCT WEIGHT	0.34 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
---------------------	------------------------

Product specifications

BOX SIZE	4-11/16"
----------	----------

	Locations
STANDARDS TYPE	NEC/CEC

CAPACITY	8.8 cubic in
COLOR	Natural
CONFIGURATION	Raised surface, two device
MATERIAL	Steel
TYPE	3/4" raised

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP586 3D drawing](#)

CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP586](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

Reserved.

