

Specifications



Eaton TP675

Eaton Crouse-Hinds series Masonry Box, (2) 1/2", (2) 3/4", 3-1/2", (2) 1/2", (2) 3/4", Steel, Single-gang, (4) 1/2", (4) 3/4", Gangable, 22.0 cubic inch capacity

General specifications

| | |
|-----------------------------|---------------------------------------|
| PRODUCT NAME | Eaton Crouse-Hinds series masonry box |
| CATALOG NUMBER | TP675 |
| UPC | 786189106756 |
| PRODUCT LENGTH/DEPTH | 3.75 in |
| PRODUCT HEIGHT | 3.75 in |
| PRODUCT WIDTH | 1.94 in |
| PRODUCT WEIGHT | 0.82 lb |



Powering Business Worldwide

Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|------------------------|------------------------|
| DEPTH | 3-1/2" |
| NUMBER OF GANGS | Single-gang |
| END KNOCKOUTS | (2) 1/2 in, (2) 3/4 in |
| SIDE KNOCKOUTS | (4) 1/2 in, (4) 3/4 in |

| | |
|-------------------------|------------------------|
| BOTTOM KNOCKOUTS | (2) 1/2 in, (2) 3/4 in |
| CAPACITY | 22 cubic in |
| MATERIAL | Steel |
| TYPE | Gangable |

Resources

CATALOGS

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

CERTIFICATION REPORTS

[Steel Masonry Boxes Canadian certification](#)

[Steel Masonry Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP675](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP675

Eaton Crouse-Hinds series Masonry Box, (2) 1/2", (2) 3/4", 3-1/2", (2) 1/2", (2) 3/4", Steel, Single-gang, (4) 1/2", (4) 3/4", Gangable, 22.0 cubic inch capacity

General specifications

| | |
|-----------------------------|---------------------------------------|
| PRODUCT NAME | Eaton Crouse-Hinds series masonry box |
| CATALOG NUMBER | TP675 |
| UPC | 786189106756 |
| PRODUCT LENGTH/DEPTH | 3.75 in |
| PRODUCT HEIGHT | 3.75 in |
| PRODUCT WIDTH | 1.94 in |
| PRODUCT WEIGHT | 0.82 lb |



Powering Business Worldwide

Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|------------------------|------------------------|
| DEPTH | 3-1/2" |
| NUMBER OF GANGS | Single-gang |
| END KNOCKOUTS | (2) 1/2 in, (2) 3/4 in |
| SIDE KNOCKOUTS | (4) 1/2 in, (4) 3/4 in |

| | |
|-------------------------|------------------------|
| BOTTOM KNOCKOUTS | (2) 1/2 in, (2) 3/4 in |
| CAPACITY | 22 cubic in |
| MATERIAL | Steel |
| TYPE | Gangable |

Resources

CATALOGS

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

CERTIFICATION REPORTS

[Steel Masonry Boxes Canadian certification](#)

[Steel Masonry Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP675](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

