

Specifications



Eaton TP691

Eaton Crouse-Hinds series Masonry Box, (4) 1/2", (4) 3/4", 3-1/2", (4) 1/2", (4) 3/4", Steel, Two-gang, (2) 1/2", (2) 3/4", 44.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series masonry box
CATALOG NUMBER	TP691
UPC	786189106916
PRODUCT LENGTH/DEPTH	3.75 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	3.75 in
PRODUCT WEIGHT	1.2 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	3-1/2"
NUMBER OF GANGS	Two-gang
END KNOCKOUTS	(4) 1/2 in, (4) 3/4 in
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in

BOTTOM KNOCKOUTS	(4) 1/2 in, (4) 3/4 in
CAPACITY	44 cubic in
MATERIAL	Steel

Resources

CATALOGS

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

CERTIFICATION REPORTS

[Steel Masonry Boxes Canadian certification](#)

[Steel Masonry Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP691](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP691

Eaton Crouse-Hinds series Masonry Box, (4) 1/2", (4) 3/4", 3-1/2", (4) 1/2", (4) 3/4", Steel, Two-gang, (2) 1/2", (2) 3/4", 44.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series masonry box
CATALOG NUMBER	TP691
UPC	786189106916
PRODUCT LENGTH/DEPTH	3.75 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	3.75 in
PRODUCT WEIGHT	1.2 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	3-1/2"
NUMBER OF GANGS	Two-gang
END KNOCKOUTS	(4) 1/2 in, (4) 3/4 in
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in

BOTTOM KNOCKOUTS	(4) 1/2 in, (4) 3/4 in
CAPACITY	44 cubic in
MATERIAL	Steel

Resources

CATALOGS

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

CERTIFICATION REPORTS

[Steel Masonry Boxes Canadian certification](#)

[Steel Masonry Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP691](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

