

Specifications



Photo is representative

Eaton TP736

Eaton Crouse-Hinds series Square Surface Cover, 4-11/16", Raised surface, Steel, For one 1.730" diameter power outlet, 9.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square surface cover
CATALOG NUMBER	TP736
UPC	786189107364
PRODUCT LENGTH/DEPTH	4.69 in
PRODUCT HEIGHT	0.06 in
PRODUCT WIDTH	4.69 in
PRODUCT WEIGHT	0.51 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
---------------------	------------------------

Product specifications

BOX SIZE	4-11/16"
----------	----------

	Locations
STANDARDS TYPE	NEC/CEC

CAPACITY	9 cubic in
CONFIGURATION	Raised surface
MATERIAL	Steel
TYPE	For one 1.730" diameter power outlet

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP736 3D drawing](#)

CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP736](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.



Specifications



Photo is representative

Eaton TP736

Eaton Crouse-Hinds series Square Surface Cover, 4-11/16", Raised surface, Steel, For one 1.730" diameter power outlet, 9.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square surface cover
CATALOG NUMBER	TP736
UPC	786189107364
PRODUCT LENGTH/DEPTH	4.69 in
PRODUCT HEIGHT	0.06 in
PRODUCT WIDTH	4.69 in
PRODUCT WEIGHT	0.51 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
---------------------	------------------------

Product specifications

BOX SIZE	4-11/16"
----------	----------

	Locations
STANDARDS TYPE	NEC/CEC

CAPACITY	9 cubic in
CONFIGURATION	Raised surface
MATERIAL	Steel
TYPE	For one 1.730" diameter power outlet

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP736 3D drawing](#)

CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP736](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.

