



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5362USBGRY Duplex Recp 20A TR Spec W/3.1A Usb Charge Gy

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | TR5362USBGRY |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Designed For Commercial Markets With Strength and Durability In Mind, This Combination Usb Charger Duplex Receptacle Features 3.1A Overall Usb Charging Capability and Is Compatible With Usb 2.0 & 3.0 Devices. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page. |
| Weight per unit | 0.3392 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|---------------------|--------------------------------|
| amperage rating | 20 |
| connection | Side & Back Wired |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Number of Wires | 3 |
| Outlet Type | Tamper-Resistant, USB-Charging |
| Phase | 1 |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|--------|-------|
| Depth | 1.392 |
| Height | 3.281 |
| Width | 1.693 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | DUPLEX RECP 20A TR SPEC W/3.1A USB CHARGE GY |
| extra long description | P&S TR5362USBGRY DUP REC 20A TR SPE |
| Features | USB-A Charging |
| Long Description | Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page. |
| Product Type | Dup Rec 20A TR Spec W/3.1A Usb CHR GY |
| Special Features | Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007031850 |
| Manufacturers Part Number | TR-5362USBGRY |
| UPC | 785007031850 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Miscellaneous residential devices |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.3392 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Commercial |
| environmental conditions | UL94 V2 |
| Mounting | BOX |
| nema rating | 5-20R |
| standard | FEDSPEC, CULUS, UL, CSA Listed, cULus, FSUL, UL Listed, RoHS, FEDSPEC |