



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR5362USBI Duplex Recp 20A TR Spec W/3.1A Usb Charge Iv

*Pass & Seymour/Legrand*

Catalog Number	TR5362USBI
Manufacturer	Pass & Seymour/Legrand
Description	Designed For Commercial Markets With Strength and Durability In Mind, This Combination Usb Charger Duplex Receptacle Features 3.1A Overall Usb Charging Capability and Is Compatible With Usb 2.0 & 3.0 Devices. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page.
Weight per unit	0.3392 (lbs/each)
Product Category	Combination Devices

### Features

amperage rating	20
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Number of Wires	3
Outlet Type	Tamper-Resistant, USB-Charging
Phase	1
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Depth	1.392
Height	3.281
Width	1.693



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	DUPLEX RECP 20A TR SPEC W/3.1A USB CHARGE IV
extra long description	P&S TR5362USBI DUP REC 20A TR SPEC
Features	USB-A Charging
Long Description	Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.
Product Type	Dup Rec 20A TR Spec W/3.1A Usb CHRG I
Special Features	Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007031584
Manufacturers Part Number	TR-5362USBI
UPC	785007031584

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.3392

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	UL94 V2
Mounting	BOX
nema rating	5-20R
standard	FEDSPEC, UL, CULUS, CSA Listed, cULus, FSUL, UL Listed, RoHS, FEDSPEC