



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR63HI TR Hosp Recp 20A 125V Iv

*Pass & Seymour/LeGrand*

|                  |                                                                            |
|------------------|----------------------------------------------------------------------------|
| Catalog Number   | TR63HI                                                                     |
| Manufacturer     | Pass & Seymour/LeGrand                                                     |
| Description      | Tamper-Resistant Hospital Grade Receptacles, Back and Side Wire, 20A, 125V |
| Weight per unit  | 0.2515 (lbs/each)                                                          |
| Product Category | Gen Purpose Recept & Surge Pro                                             |

### Features

|                     |                                                  |
|---------------------|--------------------------------------------------|
| amperage rating     | 20                                               |
| connection          | Back and side wire                               |
| Dielectric Strength | Withstands 2000V minimum                         |
| indoor/outdoor      | Indoor                                           |
| Material            | Nylon                                            |
| media               | Yes                                              |
| Number of Wires     | 3                                                |
| Outlet Type         | Tamper-Resistant, Commercial, Indoor             |
| Poles               | Double Pole                                      |
| Voltage             | 125.0 V                                          |
| Voltage Rating      | 125                                              |
| Wattage             | Electrical power is expressed in Amps and Volts. |
| Wire Size           | 14 - 10                                          |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | Ivory |
| Finish | Matte |

### Dimensions and Weight

|        |       |
|--------|-------|
| Height | 3.281 |
| Width  | .900  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | TR HOSP RECP 20A 125V IV                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| extra long description | P&S TR63HI TAMPR RESISTNT HOSP RECP                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Long Description       | Tamper-Resistant Hospital Grade Receptacles, Back and Side Wire, 20A, 125V                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Product Type           | Tampr Resistnt Hosp Recp 20A 125V I                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Special Features       | Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. Exclusive patented feature, circuit label on face allows permanent circuit identification. Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body. Easily accessed break-off, line-contact conne |

## Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007145250   |
| Manufacturers Part Number | TR63-HI          |
| UPC                       | 785007145250     |

## Taxonomies, Classifications, and Categories

|                      |                        |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type                 | Outlet                 |

## Trade Size

|          |      |
|----------|------|
| Amperage | 20.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 100    |
| Weight Per each | 0.2515 |

## Uses, Certifications, and Standards

|                          |                                         |
|--------------------------|-----------------------------------------|
| Application              | Commercial                              |
| environmental conditions | Flammability: UL94 V2                   |
| Mounting                 | WALL                                    |
| nema rating              | 5-20R                                   |
| standard                 | FEDSPEC, CULUS, UL498, CSA C22.2 No. 42 |
| Temperature Rating       | -40° - 60° C                            |