



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR8300HRED TR Compact Hosp GRD Duplex Recept 20A 125V RD

Pass & Seymour/Legrand

Catalog Number	TR8300HRED
Manufacturer	Pass & Seymour/Legrand
Description	Hospital-Grade Tamper-Resistant Compact Design Receptacle, Back and Side Wire, 20A, 125V
Weight per unit	0.1800 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Number of Wires	3
Outlet Type	Tamper-Resistant
Phase	1
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Depth	.78
Height	3.281
Width	1.322

Descriptions

Description	TR COMPACT HOSP GRD DUPLEX RECP 20A 125V RD
extra long description	P&S TR8300HRED TR COMPCT HG DUP REC
Long Description	Hospital-Grade Tamper-Resistant Compact Design Receptacle, Back and Side Wire, 20A, 125V
Product Type	TR Compct HG Dup Rec 20A 125V Red
Special Features	Built for the harshest medical environments, Pass&Seymour power indicating receptacles feature two industry-exclusive green LEDs that offer clear visual assurance of power indication at the receptacle—even with critical equipment plugged into the device. The LEDs operate independently from one another to accommodate split-circuit wiring installations. Tamper-resistant protection comes standard with each receptacle to further enhance safety.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007035179
Manufacturers Part Number	TR-8300HRED
UPC	785007035179

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	10
Package	100
Weight Per each	0.18

Uses, Certifications, and Standards

Application	Hospital grade
environmental conditions	UL94 V2
Mounting	BOX
nema rating	5-20R
standard	CULUS, CSA Listed, UL Listed, FSUL