



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TU40 Unv Multi-Volt Electromech 24HR Time Switch *Nsi Industries*

| | |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | TU40 |
| Manufacturer | Nsi Industries |
| Description | Time Switch, 120/208/240/277 V Ac, Plastic (Enclosure) Material, Screw Mount, 5-1/16 In Overall Length, 3-1/16 In Overall Width, 8-5/16 In Overall Height, 1.76 LB |
| Weight per unit | 1.8 (lbs/each) |
| Product Category | Time Switch Accessories |

Features

| | |
|----------------|---------------------|
| action | DPDT |
| Base | Screw |
| Contact Rating | 120-208-240-277 VAC |
| Number of Pins | 96 |
| Phase | Single Phase |
| Poles | 2 |
| Timing Range | 24 Hour |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=5.625 - H=8.312 - W=4.500 |
|------|-----------------------------|

Descriptions

| | |
|------------------------|-----------------------------------------------------------------|
| Description | UNV MULTI-VOLT ELECTROMECH 24HR TIME SWITCH |
| extra long description | TORK TU40 24 Hour Timer 40A 120-277 |
| Special Features | DPDT Multi Voltage 24 Hour Time Switch With 96 Captive Trippers |

Manufacturer Information

| | |
|---------------------------|----------------|
| GTIN | 00786261240002 |
| Manufacturers Part Number | TU40 |
| UPC | 786261240002 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | TIME CLOCKS |
| Type | 24 Hour Time Switch |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 1.76 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------|
| Application | NSI |
| Enclosure | NEMA 3R Plastic Indoor-Outdoor |
| environmental conditions | -31 to 116 F |
| Frequency Rating | 60 Hz |
| Mounting | Screw Mount |
| Operating Temperature | -31 to 116 F |
| standard | cULus |