



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TWHLEDAL050K Led WLPK (CLSC) Adj Output 50K

*Lithonia Lighting - Acuity*

|                  |   |
|------------------|---|
| Catalog Number   | TWHLEDAL050K  |
| Manufacturer     | Lithonia Lighting - Acuity  |
| Description      | The Lithonia Lighting TWH Led Offers A Classic Appearance and Is Powered By Advanced Leds. The TWH Led Luminaire Is Powerful Yet Energy Efficient, Capable Of Replacing Up to A 400W Metal Halide Luminaire While Saving Up to 83% In Energy Costs. Offering An Expected Service Life Of More Than 20 Years, The TWH Led Eliminates Frequent Lamp and Ballast Replacements Associated With Traditional Technologies. The TWH Led Features An Adjustable Light Output (Alo) That Allows The Contractor to Set The Light Output D |
| Weight per unit  | 24.0 (lbs/each)   |
| Product Category | Led Wallpacks   |

### Features

|                               |   |
|-------------------------------|---|
| average life                  | 100,000   |
| dimnable                      | Yes   |
| Hardware                      | Yes   |
| Lamp Included                 | Yes   |
| Lamp Type                     | LED - Static  |
| lumens                        | 2000 LM,3000 LM,4000 LM,5000 LM,6000 LM,7000 LM,8000 LM,9000 LM |
| Material                      | Aluminum  |
| Maximum Operating Temperature | 25  |
| Number of Lamps               | 1   |
| Power Source                  | Hardwired   |
| Shape                         | Rectangular   |
| Voltage Rating                | 120,208,240,277,347,480,MVOLT                                   |
| Warranty                      | 5   |
| Wattage                       | 78  |

### Material, Color, and Finish

|                             |             |
|-----------------------------|-------------|
| Color                       | Bronze      |
| color rendering index (cri) | 70          |
| color temperature           | 5000        |
| Finish                      | Gloss       |
| fixture material            | aluminum    |
| Lens Material               | Glass       |
| Style                       | Traditional |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Dimensions and Weight

|        |      |
|--------|------|
| Height | 10.5 |
| Length | 17.5 |
| Width  | 17.5 |

## Descriptions

|                        |   |
|------------------------|---|
| Description            | LED WLPK (CLSC) ADJ OUTPUT 50K  |
| extra long description | LITH TWH LED ALO 50K Glass Refracto   |
| Long Description       | The Lithonia Lighting TWH LED offers a classic appearance and is powered by advanced LEDs. The TWH LED luminaire is powerful yet energy efficient, capable of replacing up to a 400W metal halide luminaire while saving up to 83% in energy costs. Offering an expected service life of more than 20 years, the TWH LED eliminates frequent lamp and ballast replacements associated with traditional technologies. The TWH LED features an Adjustable Light Output (ALO) that allows the contractor to set the light output d |
| Product Type           | Wallpack  |

## Manufacturer Information

|                           |                   |
|---------------------------|-------------------|
| Brand                     | Lithonia Lighting |
| GTIN                      | 00191848355329    |
| Manufacturers Part Number | TWH LED ALO 50K   |
| UPC                       | 191848355329      |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING |
| Type                 | Wallpack  |

## Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight          | 30 |
| Weight Per each | 24 |

## Uses, Certifications, and Standards

|                          |                                       |
|--------------------------|---------------------------------------|
| Application              | Education,Hospitality,Offices & Banks |
| environmental conditions | OUTDOOR                               |
| Mounting                 | SURFACE                               |
| standard                 | ULDLC Standard                        |