



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UC127 1-1/2 H-Duty GRND Conn

Nsi Industries

Catalog Number	UC127
Manufacturer	Nsi Industries
Description	The Nsi Uc-127 Bronze Heavy Duty U-Bolt Clamp Is Designed to Grip Rods and Ground 1-1/2" Ips Pipes In Parallel or 90-Degree Positions With An Easily Adjusted, Durably Strong Design. The High-Copper-Content Alloy Of The Clamp Provides Excellent Conductivity and Heavy-Duty Strength, Alongside The Silicon Bronze Nuts and Lockwashers. Use This U-Bolt For Demanding Applications In Harsh Environments, Including Direct Burial In Earth or Concrete. UI Listed 467 For Grounding and Bonding. Stock Products You Can Re
Weight per unit	1.1 (lbs/each)
Product Category	Ground Rods & Grounding System

Features

Warranty	1 YEAR
----------	--------

Material, Color, and Finish

Clamp Material	250 MCM - 2/0 AWG
Insulation Material	Silicon Bronze



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	1-1/2 H-DUTY GRND CONN
extra long description	NSI UC-127 U Bolt Clamp 1 Cond. 1 1
Features	NSI grounding and bonding products rise to the occasion in a wide variety of professional environments with excellent material quality and flexible designs. These heavy-duty bronze U-bolt clamps offer a durable and reliable solution for connecting a ground cable to a pipe, using the adjustable clamping structure. The gripping jaws feature a flexible design that fits a range of pipe sizes and can attach the grounding rod and pipe either in parallel or at a 90-degree angle. The bronze body has a high copper
Long Description	The NSI UC-127 Bronze Heavy Duty U-Bolt Clamp is designed to grip rods and ground 1-1/2" IPS pipes in parallel or 90-degree positions with an easily adjusted, durably strong design. The high-copper-content alloy of the clamp provides excellent conductivity and heavy-duty strength, alongside the silicon bronze nuts and lockwashers. Use this U-bolt for demanding applications in harsh environments, including direct burial in earth or concrete. UL Listed 467 for Grounding and Bonding. Stock products you can re
Product Type	U Bolt Clamp 1 Cond. 1 1/2 Pipe 250-2/0
Special Features	1 1/2 Pipe Size

Manufacturer Information

Brand	NSi
GTIN	00662381108135
Manufacturers Part Number	UC-127
UPC	662381108135

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Heavy Duty Ground Connector For Parrallel Copper Cables

Packaging

Carton	1
Package	12
Weight Per each	1.13

Uses, Certifications, and Standards

Application	Grounding Wire
standard	UL467