

# Specifications



## Eaton UATH7330UFLCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub cover plate hub mounted, 7-jaw, 3-ph, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Al, Triplex, Side-wired, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UATH7330UFLCH
<b>UPC</b>	782116168941
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	39.88 in
<b>PRODUCT WIDTH</b>	20 in
<b>PRODUCT WEIGHT</b>	40 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Product specifications

<b>TYPE</b>	Single-position commercial or residential service
<b>AMPERAGE RATING</b>	320A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Seven-jaw
<b>PHASE</b>	Three-phase
<b>UTILITY APPROVALS</b>	FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) FL : Tallahassee City Electric
<b>LINE</b>	3/8 in stud
<b>LOAD</b>	3/8 in stud
<b>ENCLOSURE MATERIAL</b>	Aluminum
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	5 x 5 hub cover plate
<b>CONNECTION</b>	Ground connection
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>BYPASS</b>	Lever
<b>NUMBER OF SOCKETS</b>	1

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UATH7330UFLCH</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton UATH7330UFLCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub cover plate hub mounted, 7-jaw, 3-ph, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Al, Triplex, Side-wired, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UATH7330UFLCH
<b>UPC</b>	782116168941
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	39.88 in
<b>PRODUCT WIDTH</b>	20 in
<b>PRODUCT WEIGHT</b>	40 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Product specifications

<b>TYPE</b>	Single-position commercial or residential service
<b>AMPERAGE RATING</b>	320A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Seven-jaw
<b>PHASE</b>	Three-phase
<b>UTILITY APPROVALS</b>	FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) FL : Tallahassee City Electric
<b>LINE</b>	3/8 in stud
<b>LOAD</b>	3/8 in stud
<b>ENCLOSURE MATERIAL</b>	Aluminum
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	5 x 5 hub cover plate
<b>CONNECTION</b>	Ground connection
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>BYPASS</b>	Lever
<b>NUMBER OF SOCKETS</b>	1

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UATH7330UFLCH</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

