

# Eaton UBTH4330TCH

Catalog Number: UBTH4330TCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub open, 3/8 inch stud, 4-jaw, 1-ph, 3/8 inch stud, Barrel lock, Lever bypass, 3-wire, Ringless, 600 Vac



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UBTH4330TCH

### UPC

786685135472

### Product Length/Depth

5.69 in

### Product Height

36.63 in

### Product Width

15 in

### Product Weight

38 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Special features

Barrel lock provisions

### Type

Single-position commercial or residential service

### Amperage Rating

320A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

TN : Nashville Electric Service

### Line

3/8 in stud

### Load

3/8 in stud

### Number of wires

Three-wire

### Hub type

5 x 5 hub opening

### Security

Ringless

### Voltage rating

600 V

### Bypass

Lever

### Number of sockets

1

## Resources

### Brochures

Single Meter Sockets

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - SKT 320A 1P HO

### Specifications and datasheets

Eaton Specification Sheet - UBTH4330TCH

Metering Equipment - Utilities Servicing Upstate New York



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton UBTH4330TCH

Catalog Number: UBTH4330TCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub open, 3/8 inch stud, 4-jaw, 1-ph, 3/8 inch stud, Barrel lock, Lever bypass, 3-wire, Ringless, 600 Vac



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UBTH4330TCH

### UPC

786685135472

### Product Length/Depth

5.69 in

### Product Height

36.63 in

### Product Width

15 in

### Product Weight

38 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Special features

Barrel lock provisions

### Type

Single-position commercial or residential service

### Amperage Rating

320A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

TN : Nashville Electric Service

### Line

3/8 in stud

### Load

3/8 in stud

### Number of wires

Three-wire

### Hub type

5 x 5 hub opening

### Security

Ringless

### Voltage rating

600 V

### Bypass

Lever

### Number of sockets

1

## Resources

### Brochures

Single Meter Sockets

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - SKT 320A 1P HO

### Specifications and datasheets

Eaton Specification Sheet - UBTH4330TCH

Metering Equipment - Utilities Servicing Upstate New York



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)