



UHTRS223ACH 200A MTR 4-Term Horn Bypas Solid Top Ug Side-Wired

Eaton Corp

Catalog Number	UHTRS223ACH
Manufacturer	Eaton Corp
Description	Eaton Meter Socket, 1-Pos Resi Service, 200A, Under, Solid Top, #6-350 Kcmil, 4-Jaw, 1-PH, #8-350 Kcmil, Horn Bypass, GND Conn (#14-#2 Cu), Triplex, Three-Wire, Ringless, 600 Vac
Weight per unit	14.0 (lbs/each)
Product Category	Residential Single Meter Socket

Features

amperage rating	200
dimensions	4.9400 IN X 13.0000 IN X 13.0000 IN
Phase	1
Voltage Rating	600 V

Descriptions

Also Known As...	Meter Socket Meter Box
Description	200A MTR 4-TERM HORN BYPAS SOLID TOP UG SIDE-WIRED
extra long description	ETN UHTRS223ACH MtrSkt,200A,Ringless
Features	Eaton is your one-stop shop for the widest range of residential and light commercial electric meter sockets in the industry. These single-socket surface- or flush-mount outdoor enclosures come in two styles, allowing for both easy, cost-saving installation, and for the use of BR- or CH-type branch breakers. The one-piece, die-run electric meter socket enclosures eliminate tampering and extend product life. These are utility approved and can be used for residential meter socket installations, rural service
Long Description	Eaton meter socket, 1-pos resi service, 200A, Under, Solid top, #6-350 kcmil, 4-jaw, 1-ph, #8-350 kcmil, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, Three-wire, Ringless, 600 Vac
Product Type	MTRSkt, 200A, Ringless, 4-Jaw, Ug, Horn BP

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114113905
Manufacturers Part Number	UHTRS223ACH
UPC	782114113905

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Meter socket



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	14

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities -
Other	
standard	UL Listed