

# Pro-Series Xenon Low Voltage

1-Lamp, 2-Lamp, 3-Lamp, 4-Lamp Fixtures



Undercabinet Lighting

## Features

- 12-volt xenon lamps offer slightly warmer color rendering as compared to halogen
- Integral reflector spaced away from cabinet bottom maximizes light output while reducing fixture/cabinet contact temperature
- Dimmable with standard ELV type wall box dimmers or integral high/low/off rocker switch
- Hinged lens captured by spring loaded retention bar cannot accidentally fall out
- Modular design for maximum flexibility and quick installation allows up to ten fixtures to plug together using the supplied internal straight connector or optional jumper cords
- Rear wireway access cover with flush non-metallic cable clamp and push in electrical connectors facilitate wiring without opening the fixture
- Miniature die-cast fitting for flexible metal conduit, off-center knock-outs and extra mounting plate for feed-through fixture-to-fixture loop wiring increase installation versatility
- Available in Black, Brushed Bronze, Brushed Silver and Designer White finishes



## Description

The Pro-Series Xenon series offers a slightly warmer color rendering than halogen using warmer tone illumination from long-life low voltage xenon lamps. Pro-Series Xenon fixtures are optimized for fast, permanent installation, mounting either flush to the backsplash or to the front lip of cabinetry to suit project conditions and homeowner preference.

## Listing

UL/C-UL Listed

## Finishes



Black



Brushed Bronze



Brushed Silver



Designer White

## Ordering Information\*

Catalog No.	Description
UPX109-BL	9", 1 Lamp, Black
UPX109-BZ	9", 1 Lamp, Brushed Bronze
UPX109-SL	9", 1 Lamp, Brushed Silver
UPX109-WH	9", 1 Lamp, Designer White
UPX214-BL	14", 2 Lamps, Black
UPX214-BZ	14", 2 Lamps, Brushed Bronze
UPX214-SL	14", 2 Lamps, Brushed Silver
UPX214-WH	14", 2 Lamps, Designer White
UPX322-BL	22", 3 Lamps, Black
UPX322-BZ	22", 3 Lamps, Brushed Bronze
UPX322-SL	22", 3 Lamps, Brushed Silver
UPX322-WH	22", 3 Lamps, Designer White
UPX430-BL	30", 4 Lamps, Black
UPX430-BZ	30", 4 Lamps, Brushed Bronze
UPX430-SL	30", 4 Lamps, Brushed Silver
UPX430-WH	30", 4 Lamps, Designer White

\*Fixture includes: 12V 20W Bi-pin high-output xenon lamp(s)  
Mounting hardware  
Electrical connector (ULH-CONN)  
Joiner connector

## Accessories

Catalog No.	Description
JC3-8-BL	8" Jumper Cord, Black
JC3-8-WH	8" Jumper Cord, Designer White
JC3-17-BL	17" Jumper Cord, Black
JC3-17-WH	17" Jumper Cord, Designer White
JC3-26-BL	26" Jumper Cord, Black
JC3-26-WH	26" Jumper Cord, Designer White
ULH-CONN	3/8" Miniature Die-Cast Electrical Connector
ULH-CP-BL	6' Cord and Plug, Black
ULH-CP-WH	6' Cord and Plug, Designer White
ULH-DWM-BL	Direct Wire Module, Black
ULH-DWM-WH	Direct Wire Module, Designer White
UPX-LAMP	12V 20W Bi-pin High-Output Xenon Replacement Lamp

## Dimensions

