Specifications







Eaton URTRS223ACH

Eaton meter socket, Solid top, 200A, Underground, Solid top, #8-350 kcmil, Four-jaw, Single-phase, #8-350 kcmil, Sockets:1, Three-wire, Ring, 600V

General specifications	
PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	URTRS223ACH
UPC	786685125428
PRODUCT LENGTH/DEPTH	4.93 in
PRODUCT HEIGHT	13 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	13 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Powering Business Worldwide

Product specifications

TYPE	Solid top
AMPERAGE RATING	200A
FEED TYPE	Bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	TN : Knoxville Utility Board (KUB)
LINE	#8-350 kcmil
LOAD	#8-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	Solid top
SECURITY	Ring
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - URTRS223ACH

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Specifications







Eaton URTRS223ACH

Eaton meter socket, Solid top, 200A, Underground, Solid top, #8-350 kcmil, Four-jaw, Single-phase, #8-350 kcmil, Sockets:1, Three-wire, Ring, 600V

General specifications	
PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	URTRS223ACH
UPC	786685125428
PRODUCT LENGTH/DEPTH	4.93 in
PRODUCT HEIGHT	13 in
PRODUCT WIDTH	13 in
PRODUCT WEIGHT	13 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Powering Business Worldwide

Product specifications

TYPE	Solid top
AMPERAGE RATING	200A
FEED TYPE	Bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	TN : Knoxville Utility Board (KUB)
LINE	#8-350 kcmil
LOAD	#8-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	Solid top
SECURITY	Ring
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - URTRS223ACH

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.