

Eaton UTE5213CCH

Catalog Number: UTE5213CCH

Eaton meter socket, Comm, 200A, Over/under, 3-5/16 inch hub cover plate, #6-350 kcmil, 5-jaw, 1-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, Three-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTE5213CCH

UPC

786685271361

Product Length/Depth

4.94 in

Product Height

19 in

Product Width

13 in

Product Weight

26 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Commercial

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Five-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power

NM : El Paso Electric

TX : El Paso Electric

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

NM : Public Service Company of New Mexico (PNM)

WI : WE Energies / Wisconsin Public Service (WPS)

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Three-wire

Hub type

3-5/16 in hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Specifications and datasheets

[Eaton Specification Sheet - UTE5213CCH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton UTE5213CCH

Catalog Number: UTE5213CCH

Eaton meter socket, Comm, 200A, Over/under, 3-5/16 inch hub cover plate, #6-350 kcmil, 5-jaw, 1-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, Three-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTE5213CCH

UPC

786685271361

Product Length/Depth

4.94 in

Product Height

19 in

Product Width

13 in

Product Weight

26 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Commercial

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Five-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power

NM : El Paso Electric

TX : El Paso Electric

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

NM : Public Service Company of New Mexico (PNM)

WI : WE Energies / Wisconsin Public Service (WPS)

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Three-wire

Hub type

3-5/16 in hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Specifications and datasheets

Eaton Specification Sheet - UTE5213CCH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)