

# Eaton UTE7213CCH

Catalog Number: UTE7213CCH

Eaton meter socket, Comm, 200A, Over/under, 3-5/16 inch hub cover plate, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UTE7213CCH

### UPC

786685351247

### Product Length/Depth

4.94 in

### Product Height

19 in

### Product Width

13 in

### Product Weight

25 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

Commercial

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Seven-jaw

### Phase

Three-phase

### Utility approvals

WI : WE Energies / Wisconsin Public Service (WPS)

### Line

#6-350 kcmil

### Load

#6-350 kcmil

### Number of wires

Four-wire

### Hub type

3-5/16 in hub cover plate

### Security

Ringless

### Voltage rating

600 V

### Bypass

Lever

### Number of sockets

1

## Resources

### Brochures

Single Meter Sockets

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - SKT 200A 3P HCP

### Specifications and datasheets

Eaton Specification Sheet - UTE7213CCH



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton UTE7213CCH

Catalog Number: UTE7213CCH

Eaton meter socket, Comm, 200A, Over/under, 3-5/16 inch hub cover plate, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UTE7213CCH

### UPC

786685351247

### Product Length/Depth

4.94 in

### Product Height

19 in

### Product Width

13 in

### Product Weight

25 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

Commercial

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Seven-jaw

### Phase

Three-phase

### Utility approvals

WI : WE Energies / Wisconsin Public Service (WPS)

### Line

#6-350 kcmil

### Load

#6-350 kcmil

### Number of wires

Four-wire

### Hub type

3-5/16 in hub cover plate

### Security

Ringless

### Voltage rating

600 V

### Bypass

Lever

### Number of sockets

1

## Resources

### Brochures

Single Meter Sockets

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - SKT 200A 3P HCP

### Specifications and datasheets

Eaton Specification Sheet - UTE7213CCH



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)