

Specifications



Eaton UTE7213THLCH

Eaton meter socket, Comm, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, 1-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton meter socket |
| CATALOG NUMBER | UTE7213THLCH |
| UPC | 786685351278 |
| PRODUCT LENGTH/DEPTH | 4.94 in |
| PRODUCT HEIGHT | 19 in |
| PRODUCT WIDTH | 13 in |
| PRODUCT WEIGHT | 25 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| CERTIFICATIONS | UL Listed |



Powering Business Worldwide

Product specifications

| | |
|--------------------------|---|
| TYPE | Commercial |
| AMPERAGE RATING | 200A |
| FEED TYPE | Top/bottom |
| NUMBER OF JAWS | Seven-jaw |
| PHASE | Single-phase |
| UTILITY APPROVALS | TX : Oncor TX : Pedernales Electric Cooperative |
| LINE | #6-350 kcmil |
| LOAD | #6-350 kcmil |
| NUMBER OF WIRES | Three-wire |
| HUB TYPE | 5 x 5 hub opening |
| CONNECTION | Ground connection |
| SECURITY | Ringless |
| VOLTAGE RATING | 600 V |
| BYPASS | Lever |
| NUMBER OF SOCKETS | 1 |

Resources

| | |
|--------------------------------------|--|
| CATALOGS | Residential and Light Commercial, Metering Products, Volume 1 Tab 4 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - UTE7213THLCH |
| WARRANTY GUIDES | Selling Policy 25-000 - Distribution and Control Products and Services |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton UTE7213THLCH

Eaton meter socket, Comm, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, 1-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton meter socket |
| CATALOG NUMBER | UTE7213THLCH |
| UPC | 786685351278 |
| PRODUCT LENGTH/DEPTH | 4.94 in |
| PRODUCT HEIGHT | 19 in |
| PRODUCT WIDTH | 13 in |
| PRODUCT WEIGHT | 25 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| CERTIFICATIONS | UL Listed |



Powering Business Worldwide

Product specifications

| | |
|--------------------------|---|
| TYPE | Commercial |
| AMPERAGE RATING | 200A |
| FEED TYPE | Top/bottom |
| NUMBER OF JAWS | Seven-jaw |
| PHASE | Single-phase |
| UTILITY APPROVALS | TX : Oncor TX : Pedernales Electric Cooperative |
| LINE | #6-350 kcmil |
| LOAD | #6-350 kcmil |
| NUMBER OF WIRES | Three-wire |
| HUB TYPE | 5 x 5 hub opening |
| CONNECTION | Ground connection |
| SECURITY | Ringless |
| VOLTAGE RATING | 600 V |
| BYPASS | Lever |
| NUMBER OF SOCKETS | 1 |

Resources

| | |
|--------------------------------------|--|
| CATALOGS | Residential and Light Commercial, Metering Products, Volume 1 Tab 4 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - UTE7213THLCH |
| WARRANTY GUIDES | Selling Policy 25-000 - Distribution and Control Products and Services |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

