

Eaton UTH5213BNDCH

Catalog Number: UTH5213BNDCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, Small hub open, #6-350 kcmil, 5-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

UPC

782113684062

Product Height

19 in

Product Weight

26 lb

Catalog Number

UTH5213BNDCH

Product Length/Depth

4.94 in

Product Width

13 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Five-jaw

Phase

Three-phase

Utility approvals

KY : Louisville Gas & Electric/Kentucky Utilities

TX : Oncor

TX : Pedernales Electric Cooperative

NM : Texas-New Mexico Power (TNMP)

TX : Texas-New Mexico Power (TNMP)

WI : WE Energies / Wisconsin Public Service (WPS)

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Four-wire

Hub type

Small hub opening

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Drawings

[Dimensional Drawing - SKT 200A 5T HO](#)

Specifications and datasheets

[Metering Equipment - Utilities Servicing Texas](#)

[Eaton Specification Sheet - UTH5213BNDCH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton UTH5213BNDCH

Catalog Number: UTH5213BNDCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, Small hub open, #6-350 kcmil, 5-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

UPC

782113684062

Product Height

19 in

Product Weight

26 lb

Certifications

UL Listed

Catalog Number

UTH5213BNDCH

Product Length/Depth

4.94 in

Product Width

13 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Five-jaw

Phase

Three-phase

Utility approvals

KY : Louisville Gas & Electric/Kentucky Utilities

TX : Oncor

TX : Pedernales Electric Cooperative

NM : Texas-New Mexico Power (TNMP)

TX : Texas-New Mexico Power (TNMP)

WI : WE Energies / Wisconsin Public Service (WPS)

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Four-wire

Hub type

Small hub opening

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Drawings

[Dimensional Drawing - SKT 200A 5T HO](#)

Specifications and datasheets

[Metering Equipment - Utilities Servicing Texas](#)

[Eaton Specification Sheet - UTH5213BNDCH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)