

# Specifications



## Eaton UTH5213BNDCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, Small hub open, #6-350 kcmil, 5-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTH5213BNDCH
<b>UPC</b>	782113684062
<b>PRODUCT LENGTH/DEPTH</b>	4.94 in
<b>PRODUCT HEIGHT</b>	19 in
<b>PRODUCT WIDTH</b>	13 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Single-position commercial or residential service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Five-jaw
<b>PHASE</b>	Three-phase
<b>UTILITY APPROVALS</b>	KY : Louisville Gas & Electric/Kentucky Utilities TX : Oncor TX : Pedernales Electric Cooperative NM : Texas-New Mexico Power (TNMP) TX : Texas-New Mexico Power (TNMP) WI : WE Energies / Wisconsin Public Service (WPS)
<b>LINE</b>	#6-350 kcmil
<b>LOAD</b>	#6-350 kcmil
<b>NUMBER OF WIRES</b>	Four-wire
<b>HUB TYPE</b>	Small hub opening
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>BYPASS</b>	Lever
<b>NUMBER OF SOCKETS</b>	1

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UTH5213BNDCH](#)

### WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

---

Reserved.



# Specifications



## Eaton UTH5213BNDCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, Small hub open, #6-350 kcmil, 5-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTH5213BNDCH
<b>UPC</b>	782113684062
<b>PRODUCT LENGTH/DEPTH</b>	4.94 in
<b>PRODUCT HEIGHT</b>	19 in
<b>PRODUCT WIDTH</b>	13 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Single-position commercial or residential service
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Five-jaw
<b>PHASE</b>	Three-phase
<b>UTILITY APPROVALS</b>	KY : Louisville Gas & Electric/Kentucky Utilities TX : Oncor TX : Pedernales Electric Cooperative NM : Texas-New Mexico Power (TNMP) TX : Texas-New Mexico Power (TNMP) WI : WE Energies / Wisconsin Public Service (WPS)
<b>LINE</b>	#6-350 kcmil
<b>LOAD</b>	#6-350 kcmil
<b>NUMBER OF WIRES</b>	Four-wire
<b>HUB TYPE</b>	Small hub opening
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>BYPASS</b>	Lever
<b>NUMBER OF SOCKETS</b>	1

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UTH5213BNDCH](#)

### WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

---

Reserved.

