

Eaton UTH7233UCH

Catalog Number: UTH7233UCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTH7233UCH

UPC

782116104208

Product Length/Depth

5.63 in

Product Height

27 in

Product Width

16 in

Product Weight

31 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Three-phase

Utility approvals

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Four-wire

Hub type

5 x 5 hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - SKT 200A 3P HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - UTH7233UCH](#)

[Metering Equipment - Utilities Servicing Texas](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton UTH7233UCH

Catalog Number: UTH7233UCH

Eaton meter socket, 1-pos commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTH7233UCH

UPC

782116104208

Product Length/Depth

5.63 in

Product Height

27 in

Product Width

16 in

Product Weight

31 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Single-position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Seven-jaw

Phase

Three-phase

Utility approvals

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

Line

#6-350 kcmil

Load

#6-350 kcmil

Number of wires

Four-wire

Hub type

5 x 5 hub cover plate

Security

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - SKT 200A 3P HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - UTH7233UCH](#)

[Metering Equipment - Utilities Servicing Texas](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia