

Specifications



Eaton USTS131L143CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 1.25 inch hub mounted, 13-jaw, Factory wired test switch, 600 Vac, 1-socket

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	USTS131L143CH
UPC	782116199976
PRODUCT LENGTH/DEPTH	4.35 in
PRODUCT HEIGHT	20 in
PRODUCT WIDTH	12 in
PRODUCT WEIGHT	18 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Instrument rated socket
AMPERAGE RATING	20A
FEED TYPE	Top/bottom
NUMBER OF JAWS	13-jaw
PHASE	Three-phase
UTILITY APPROVALS	TN : Middle Tennessee EMC
ENCLOSURE MATERIAL	16 GA GALV STEEL
NUMBER OF WIRES	Four-wire
HUB TYPE	1-1/4 in bolt-on hub
SECURITY	Ringless
VOLTAGE RATING	600 V
ACCESSORIES	Factory wired test switch
NUMBER OF SOCKETS	1

Resources

CATALOGS

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - USTS131L143CH](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton USTS131L143CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 1.25 inch hub mounted, 13-jaw, Factory wired test switch, 600 Vac, 1-socket

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	USTS131L143CH
UPC	782116199976
PRODUCT LENGTH/DEPTH	4.35 in
PRODUCT HEIGHT	20 in
PRODUCT WIDTH	12 in
PRODUCT WEIGHT	18 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Instrument rated socket
AMPERAGE RATING	20A
FEED TYPE	Top/bottom
NUMBER OF JAWS	13-jaw
PHASE	Three-phase
UTILITY APPROVALS	TN : Middle Tennessee EMC
ENCLOSURE MATERIAL	16 GA GALV STEEL
NUMBER OF WIRES	Four-wire
HUB TYPE	1-1/4 in bolt-on hub
SECURITY	Ringless
VOLTAGE RATING	600 V
ACCESSORIES	Factory wired test switch
NUMBER OF SOCKETS	1

Resources

CATALOGS

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - USTS131L143CH](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

