

Eaton USTS131L143CH

Catalog Number: USTS131L143CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 1.25 inch hub mounted, 13-jaw, Factory wired test switch, 600 Vac, 1-socket



General specifications

Product Name

Eaton meter socket

Catalog Number

USTS131L143CH

UPC

782116199976

Product Length/Depth

4.35 in

Product Height

20 in

Product Width

12 in

Product Weight

18 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Instrument rated socket

Amperage Rating

20A

Feed type

Top/bottom

Number of jaws

13-jaw

Phase

Three-phase

Utility approvals

TN : Middle Tennessee EMC

Enclosure material

16 GA GALV STEEL

Number of wires

Four-wire

Hub type

1-1/4 in bolt-on hub

Security

Ringless

Voltage rating

600 V

Accessories

Factory wired test switch

Number of sockets

1

Resources

Brochures

Single Meter Sockets

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT/SW 20A 13T FW 1-1/4

Specifications and datasheets

Eaton Specification Sheet - USTS131L143CH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton USTS131L143CH

Catalog Number: USTS131L143CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 1.25 inch hub mounted, 13-jaw, Factory wired test switch, 600 Vac, 1-socket



General specifications

Product Name

Eaton meter socket

Catalog Number

USTS131L143CH

UPC

782116199976

Product Length/Depth

4.35 in

Product Height

20 in

Product Width

12 in

Product Weight

18 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Instrument rated socket

Amperage Rating

20A

Feed type

Top/bottom

Number of jaws

13-jaw

Phase

Three-phase

Utility approvals

TN : Middle Tennessee EMC

Enclosure material

16 GA GALV STEEL

Number of wires

Four-wire

Hub type

1-1/4 in bolt-on hub

Security

Ringless

Voltage rating

600 V

Accessories

Factory wired test switch

Number of sockets

1

Resources

Brochures

Single Meter Sockets

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT/SW 20A 13T FW 1-1/4

Specifications and datasheets

Eaton Specification Sheet - USTS131L143CH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia