

Eaton UT2R2332UCH

Catalog Number: UT2R2332UCH

Eaton meter socket, Multi position commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications



Product Name

Eaton meter socket

Catalog Number

UT2R2332UCH

UPC

782116136827

Product Length/Depth

5.38 in

Product Height

14.13 in

Product Width

24.31 in

Product Weight

30 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Multiple position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

Line

#6-350 kcmil

Load

#8-250 kcmil

Number of wires

Three-wire

Hub type

5 x 5 hub cover plate

Security

Ringless

Voltage rating

600 V

Number of sockets

2

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT/2 GANG 200A 1P HCP

Specifications and datasheets

Eaton Specification Sheet - UT2R2332UCH

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton UT2R2332UCH

Catalog Number: UT2R2332UCH

Eaton meter socket, Multi position commercial or resi service, 200A, Over/under, 5x5 inch hub cover plate, #6-350 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications



Product Name

Eaton meter socket

Catalog Number

UT2R2332UCH

UPC

782116136827

Product Length/Depth

5.38 in

Product Height

14.13 in

Product Width

24.31 in

Product Weight

30 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Multiple position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

Line

#6-350 kcmil

Load

#8-250 kcmil

Number of wires

Three-wire

Hub type

5 x 5 hub cover plate

Security

Ringless

Voltage rating

600 V

Number of sockets

2

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT/2 GANG 200A 1P HCP

Specifications and datasheets

Eaton Specification Sheet - UT2R2332UCH

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)