

Specifications



Eaton UTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTRS101BE
UPC	786685217710
PRODUCT LENGTH/DEPTH	3.61 in
PRODUCT HEIGHT	11.05 in
PRODUCT WIDTH	8.22 in
PRODUCT WEIGHT	6.46 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Product specifications

TYPE	Single-position residential service
AMPERAGE RATING	125A
FEED TYPE	Overhead
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	<p>ME : Central Maine Power NM : El Paso Electric TX : El Paso Electric AL : Alabama Power ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company) MO : Empire District Electric OK : Empire District Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy AL : Huntsville Utilities FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) TX : Pedernales Electric Cooperative NM : Public Service Company of New Mexico (PNM) SC : South Carolina Electric and Gas (SCE&G)</p>
LINE	#8-2/0 AWG
LOAD	#8-2/0 AWG
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub opening
CONNECTION	Ground connection
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTRS101BE

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton UTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTRS101BE
UPC	786685217710
PRODUCT LENGTH/DEPTH	3.61 in
PRODUCT HEIGHT	11.05 in
PRODUCT WIDTH	8.22 in
PRODUCT WEIGHT	6.46 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Product specifications

TYPE	Single-position residential service
AMPERAGE RATING	125A
FEED TYPE	Overhead
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	<p>ME : Central Maine Power NM : El Paso Electric TX : El Paso Electric AL : Alabama Power ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company) MO : Empire District Electric OK : Empire District Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy AL : Huntsville Utilities FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric) TX : Pedernales Electric Cooperative NM : Public Service Company of New Mexico (PNM) SC : South Carolina Electric and Gas (SCE&G)</p>
LINE	#8-2/0 AWG
LOAD	#8-2/0 AWG
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub opening
CONNECTION	Ground connection
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTRS101BE

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

