




# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## V2010A3 2000 Lge Cap Ent End Fit Iv Wiremold/Legrand

Catalog Number	V2010A3
Manufacturer	Wiremold/Legrand
Description	1/2" Trade Size Kos Located On End, Sides, and Bottom Of Fitting. 3/4" Kos On Bottom and Rear. Includes Ground Screw.</P>
Weight per unit	0.7300 (lbs/each)
Product Category	Metallic Raceway & Accessories

### Features

Enclosure Type	Steel
Voltage	125.0 V

### Descriptions

Description	2000 LGE CAP ENT END FIT IV
extra long description	WM V2010A3 2000 LGE CAP ENT END FIT
Long Description	1/2" trade size KOs located on end, sides, and bottom of fitting. 3/4" KOs on bottom and rear. Includes ground screw.</p>
Product Type	2000 Lge Cap Ent End Fit Ivory
Special Features	Steel Raceway, Compact low profile design, Full range of fittings, one and two - gang device boxes.

### Manufacturer Information

Brand	WIREMOLD
GTIN	00786776009606
Manufacturers Part Number	V2010A3
UPC	786776009606

### Taxonomies, Classifications, and Categories

Category Description	Panduit & Wiremold Metallic & Non-Metallic Raceways
Type	Plugmold

### Trade Size

Amperage	15.0
----------	------

### Packaging

Carton	1
Weight Per each	0.73



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

environmental conditions  
standard

Dry Interior Locations

ROHS, NAFTA, CULUS, cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover & Plugmold Series w/Snapicoil Haarness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. cULus Listed Raceway: File E4376 Guide RJBT. Fittings: File E41751 Guide RJPR. Base & Black Cover: Meets Article 386 of NEC. Meets Section 12-600 of CEC.