

Eaton V65W-G

Catalog Number: V65W-G

Eaton Crouse-Hinds series V-Spring telescoping light pole,
Galvanized steel, Wall mount

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series V-Spring telescoping light pole	V65W-G
	UPC
	662276470019
Product Length/Depth	Product Height
73.5 in	6.57 in
Product Width	Product Weight
6.57 in	53 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Ingress protection (IP) ratings

IP66

Product specifications

Mounting style

Wall

Material

Galvanized steel

Resources

3D CAD drawing package

[Eaton Crouse-Hinds V65W-G 3D drawing](#)

3D models

[SP3D Design Package - V-Spring Telescoping Safety Light Pole](#)

Brochures

[Crouse-Hinds series V-Spring Telescoping Safety Light Pole brochure](#)

Catalogs

[Crouse-Hinds series V-Spring Telescoping Safety Light Pole catalog page](#)

Certification reports

[V-Spring Telescoping Safety Light Pole Canadian certification](#)

Installation instructions

[IF 1762 - V-Spring Telescoping Safety Light Pole](#)

Specifications and datasheets

[V-Spring Telescoping Safety Light Pole](#)

[Eaton Specification Sheet - V65W-G](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton V65W-G

Catalog Number: V65W-G

Eaton Crouse-Hinds series V-Spring telescoping light pole,
Galvanized steel, Wall mount

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series V-Spring telescoping light pole	V65W-G
	UPC
	662276470019
Product Length/Depth	Product Height
73.5 in	6.57 in
Product Width	Product Weight
6.57 in	53 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Ingress protection (IP) ratings

IP66

Product specifications

Mounting style

Wall

Material

Galvanized steel

Resources

3D CAD drawing package

[Eaton Crouse-Hinds V65W-G 3D drawing](#)

3D models

[SP3D Design Package - V-Spring Telescoping Safety Light Pole](#)

Brochures

[Crouse-Hinds series V-Spring Telescoping Safety Light Pole brochure](#)

Catalogs

[Crouse-Hinds series V-Spring Telescoping Safety Light Pole catalog page](#)

Certification reports

[V-Spring Telescoping Safety Light Pole Canadian certification](#)

Installation instructions

[IF 1762 - V-Spring Telescoping Safety Light Pole](#)

Specifications and datasheets

[V-Spring Telescoping Safety Light Pole](#)

[Eaton Specification Sheet - V65W-G](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)