

Eaton V48M28T12EE

Catalog Number: V48M28T12EE

Eaton General purpose ventilated transformer, DT-3 (3-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 208Y/120V, 150°C rise w/ 200°C insulation system, 112.5 kVA, EE

Photo is representative



General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton General purpose ventilated transformer | V48M28T12EE |
| | UPC |
| | 786680019371 |
| Product Length/Depth | Product Height |
| 23.42 in | 32.02 in |
| Product Width | Product Weight |
| 28.22 in | 793 lb |
| Warranty | Compliances |
| Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | |
| | Certifications |
| | UL Listed |
| | Catalog Notes |
| | NEMA TP-1 efficient |

Physical Attributes

Coil material

Aluminum

Frame

916A

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

480 V

Secondary Voltage

208 Y/120 V

Temperature rise

150 °C rise

Volt ampere rating

112.5 kVA

Miscellaneous

Weathershield

WS19

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28T12EE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton V48M28T12EE

Catalog Number: V48M28T12EE

Eaton General purpose ventilated transformer, DT-3 (3-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 208Y/120V, 150°C rise w/ 200°C insulation system, 112.5 kVA, EE

Photo is representative



General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton General purpose ventilated transformer | V48M28T12EE |
| | UPC |
| | 786680019371 |
| Product Length/Depth | Product Height |
| 23.42 in | 32.02 in |
| Product Width | Product Weight |
| 28.22 in | 793 lb |
| Warranty | Compliances |
| Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | Certifications |
| | UL Listed |
| | Catalog Notes |
| | NEMA TP-1 efficient |

Physical Attributes

Coil material

Aluminum

Frame

916A

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

480 V

Secondary Voltage

208 Y/120 V

Temperature rise

150 °C rise

Volt ampere rating

112.5 kVA

Miscellaneous

Weathershield

WS19

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - V48M28T12EE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)