

Eaton V48M28T75EE

Catalog Number: V48M28T75EE

Eaton General purpose ventilated transformer, DT-3 (3-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 208Y/120V, 150°C rise w/ 200°C insulation system, 75 kVA, EE



General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M28T75EE
	UPC
	786680019364
Product Length/Depth	Product Height
22 in	39 in
Product Width	Product Weight
29 in	544 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	Certifications
	UL Listed
	Catalog Notes
	NEMA TP-1 efficient

Physical Attributes

Coil material

Aluminum

Frame

914D

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

480 V

Secondary Voltage

208 Y/120 V

Temperature rise

150 °C rise

Volt ampere rating

75 kVA

Miscellaneous

Weathershield

WS39

Resources

Specifications and datasheets

[Eaton Specification Sheet - V48M28T75EE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton V48M28T75EE

Catalog Number: V48M28T75EE

Eaton General purpose ventilated transformer, DT-3 (3-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 208Y/120V, 150°C rise w/ 200°C insulation system, 75 kVA, EE



General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48M28T75EE
	UPC
	786680019364
Product Length/Depth	Product Height
22 in	39 in
Product Width	Product Weight
29 in	544 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	Certifications
	UL Listed
	Catalog Notes
	NEMA TP-1 efficient

Physical Attributes

Coil material

Aluminum

Frame

914D

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

480 V

Secondary Voltage

208 Y/120 V

Temperature rise

150 °C rise

Volt ampere rating

75 kVA

Miscellaneous

Weathershield

WS39

Resources

Specifications and datasheets

[Eaton Specification Sheet - V48M28T75EE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)