

# Eaton V65W-G

Catalog Number: V65W-G

Eaton Crouse-Hinds series V-Spring telescoping light pole,  
Galvanized steel, Wall mount

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series V-Spring telescoping light pole	V65W-G
	UPC
	662276470019
Product Length/Depth	Product Height
73.5 in	6.57 in
Product Width	Product Weight
6.57 in	53 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

### Ingress protection (IP) ratings

IP66

## Product specifications

### Mounting style

Wall

### Material

Galvanized steel

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds V65W-G 3D drawing](#)

### 3D models

[SP3D Design Package - V-Spring Telescoping Safety Light Pole](#)

### Brochures

[Crouse-Hinds series V-Spring Telescoping Safety Light Pole brochure](#)

### Catalogs

[Crouse-Hinds series V-Spring Telescoping Safety Light Pole catalog page](#)

### Certification reports

[V-Spring Telescoping Safety Light Pole Canadian certification](#)

### Installation instructions

[IF 1762 - V-Spring Telescoping Safety Light Pole](#)

### Specifications and datasheets

[V-Spring Telescoping Safety Light Pole](#)

[Eaton Specification Sheet - V65W-G](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton V65W-G

Catalog Number: V65W-G

Eaton Crouse-Hinds series V-Spring telescoping light pole,  
Galvanized steel, Wall mount

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series V-Spring telescoping light pole	V65W-G
	UPC
	662276470019
Product Length/Depth	Product Height
73.5 in	6.57 in
Product Width	Product Weight
6.57 in	53 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

### Ingress protection (IP) ratings

IP66

## Product specifications

### Mounting style

Wall

### Material

Galvanized steel

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds V65W-G 3D drawing](#)

### 3D models

[SP3D Design Package - V-Spring Telescoping Safety Light Pole](#)

### Brochures

[Crouse-Hinds series V-Spring Telescoping Safety Light Pole brochure](#)

### Catalogs

[Crouse-Hinds series V-Spring Telescoping Safety Light Pole catalog page](#)

### Certification reports

[V-Spring Telescoping Safety Light Pole Canadian certification](#)

### Installation instructions

[IF 1762 - V-Spring Telescoping Safety Light Pole](#)

### Specifications and datasheets

[V-Spring Telescoping Safety Light Pole](#)

[Eaton Specification Sheet - V65W-G](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)