



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VHBLEDLD118WUNVL 134W Led Highbay 40K 18000LM Dim 120-277V Wide *Cooper Lighting Solutions*

| | |
|------------------|---|
| Catalog Number | VHBLEDLD118WUNVL |
| Manufacturer | Cooper Lighting Solutions |
| Description | Led High Bay, White Enamel, CRS;Aluminum, 120/277 V Ac, 0.36 A @ 277 V, 160 W, 60000 H Average Life, 18568 LM Brightness (Lumens), 3500 K;4000 K;5000 K, 85, Non Dimmable, Wide Beam Spread, Surface/Chain Mount, 18-27/32 In Length, 14-19/32 In Width, 3-13/16 In Height, 15 LB |
| Weight per unit | 15.0 (lbs/each) |
| Product Category | Led Highbay Lighting |

Features

| | |
|-----------------|----------------|
| amperage rating | 0.36 (at 277V) |
| Ballast Type | N/A |
| Lamp Type | LED |

Material, Color, and Finish

| | |
|-------|---------|
| Style | (blank) |
|-------|---------|

Descriptions

| | |
|------------------------|------------------------------------|
| Description | VHBLEDLD118WUNV840CD1U |
| extra long description | CLS VHB-18-W-UNV-L840-CD-U VHB 180 |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | Cooper Metalux |
| GTIN | 00080083785919 |
| Manufacturers Part Number | VHB-18-W-UNV-L840-CD-U |
| UPC | 080083785919 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING |
| Type | INDUSTRIAL |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 15 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting
standard

High Bay

cULus Listed - Damp Location;40 Degree C Ambient Temperature
Rating;RoHS Compliant;LM79/LM80 Compliant;DLC Qualified