

# Specifications

## Eaton VMVL-7-UNV1



Photo is representative

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 127 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 61W

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Champ VMVL LED light fixture
<b>CATALOG NUMBER</b>	VMVL-7-UNV1
<b>UPC</b>	662276861015
<b>PRODUCT LENGTH/DEPTH</b>	13 in
<b>PRODUCT HEIGHT</b>	13.13 in
<b>PRODUCT WIDTH</b>	12.75 in
<b>PRODUCT WEIGHT</b>	20.8 lb



### Certifications and compliances

**AREA CLASSIFICATION** Hazardous/Classified Locations

### Product specifications

**LUMENS** 7000

<b>STANDARDS TYPE</b>	NEC/CEC IEC IECEX/ATEX
<b>NEC HAZARDOUS RATING</b>	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
<b>IECEX/ATEX HAZARDOUS RATING</b>	Zone 21
<b>NEMA RATING</b>	4X
<b>INGRESS PROTECTION (IP) RATINGS</b>	IP66

<b>LUMENS PER WATT</b>	127
<b>COLOR TEMPERATURE</b>	Cool white
<b>MOUNTING METHOD</b>	No mounting module
<b>OPTICAL DISTRIBUTION</b>	Type V
<b>GUARD TYPE</b>	No guard
<b>VOLTAGE RATING</b>	100-277 Vac, 127-250 Vdc
<b>FREQUENCY RATING</b>	50/60 Hz
<b>WATTAGE</b>	61W
<b>DIMMING</b>	Dimmable driver
<b>POWER FACTOR</b>	> 0.90
<b>EQUIVALENT LUMINAIRE</b>	175W HID
<b>MATERIAL</b>	Die cast aluminum
<b>LENS MATERIAL</b>	Heat and impact resistant glass

## Resources

<b>3D MODELS</b>	<a href="#">SP3D Design Package - Champ VMVL LED Hazardous Area Light Fixtures</a>
<b>BROCHURES</b>	<a href="#">Crouse-Hinds series Global LED lighting portfolio</a>  <a href="#">Crouse-Hinds series DLC approved lighting products</a>  <a href="#">Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure</a>
<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 1888 - Champ VMVL and PVML Driver Replacement</a>  <a href="#">IF 1882 - Champ VMVL and PVML LED luminaires</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Champ VMV LED Hazardous Area</a>  <a href="#">Eaton Specification Sheet - VMVL-7-UNV1</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

