



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WCYB Yel Twist-On Wire Conn

*Nsi Industries*

Catalog Number	WCYB
Manufacturer	Nsi Industries
Description	The Easy-Twist WC-Y-B 500 Bag Of Standard-Style Yellow Wire Connectors Are Designed For Use On Copper Wires In The 22-8 Awg Size Range. Theyâ€™re Made Of Flame-Retardant Thermoplastic Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You Need to Connect Wires.
Weight per unit	2.1 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Thermoplastic
Number of Conductors	1
Voltage Rating	600
Warranty	1 YEAR
Wire Type	CU Wire Only

### Material, Color, and Finish

Color	Yellow
Finish	Thermoplastic

### Dimensions and Weight

Size	H=.969 - W=.551 - ID=.236
------	---------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	YEL TWIST-ON WIRE CONN
extra long description	NSI WC-Y-B Easy-Twist Yellow - 500
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. The expert team at NSI designed these connectors with key convenience and performance features for electrical in
Long Description	The Easy-Twist WC-Y-B 500 Bag of Standard-Style Yellow Wire Connectors are designed for use on copper wires in the 22-8 AWG size range. They are made of flame-retardant thermoplastic rated for a maximum temperature of 105°C (221°F). The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or anywhere else you need to connect wires.
Product Type	Easy-Twist Yellow - 500 Bag
Special Features	Standard Yellow Wire Connectors - 500 Pcs Bag

## Manufacturer Information

Brand	NSi
GTIN	00662381140326
Manufacturers Part Number	WC-Y-B
UPC	662381140326

## Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Standard Wire Connectors

## Availability

minimum qty	500
-------------	-----

## Packaging

Carton	1
Package	500
Weight Per each	2.14



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C
Temperature Rating	105 C