



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF100LP 67X36X16 N3R Weatherflo HC, W/Fan

Hoffman Enclosures, Inc.

| | |
|------------------|---|
| Catalog Number | WF100LP |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Weatherflo With Fan Type 3R, 67.00X36.00X16.00, White, Aluminum |
| Weight per unit | 161.0 (lbs/each) |
| Product Category | Nema Types 3 & 3R Metallic Enc |

Features

| | |
|-----------|----------|
| ip rating | IP32 |
| Material | Aluminum |

Material, Color, and Finish

| | |
|------------|--------------|
| Color | Signal White |
| Color Code | RAL 9003 |
| Finish | Galvanized |

Dimensions and Weight

| | |
|--------|----------------------|
| Depth | 16 |
| Height | 67 |
| Size | 67.00x36.00x16.00 in |
| Width | 36 |

Descriptions

| | |
|------------------------|--|
| Description | 67X36X16 N3R WEATHERFLO HC,W/FAN |
| extra long description | NVENT HOF WF100LP 60HX36WX16D |
| Features | WeatherFlo Enclosures feature a forced-air ventilation system for cooling drives or other high-heat producing equipment in outdoor applications. |
| Long Description | WeatherFlo with Fan Type 3R, 67.00x36.00x16.00, White, Aluminum |
| Product Type | 60HX36WX16D |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510156848 |
| Manufacturers Part Number | WF100LP |
| UPC | 783510156848 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | STEEL JUNCTION BOXES |
| Type | Mild Steel Wall Mounted Industrial Enclosures |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 161 |

Uses, Certifications, and Standards

| | |
|-------------|-----------------------------------|
| Application | Controls and Drives |
| nema rating | 3R Weather-resistant, except dust |