



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

WF6AL020SWW590CR 6" Led Wafer 27K/3K/35K/4K/5K 800/1050/1300LM

Lithonia Lighting



Catalog Number	WF6AL020SWW590CR
Manufacturer	Lithonia Lighting
Description	The 6IN Canless Wafer Downlight Has An Innovative, Slim Design That Installs Quickly and Easily Into As Little As 3IN Of Plenum Space Allowing For It to Fit Into Ceiling Spaces Where Most Traditional Recessed Housings Do Not. Wafers Install Directly Into Dry Wall Eliminating The Need For Recessed Housings. Once Installed, Our Wafer Provides An All-In-One Design Featuring Switchable White Color Temperature and Adjustable Lumen Output Technology. This Technology Gives The Ultimate In Flexibility, Providing Y
Weight per unit	1.4 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1050 LM,1300 LM,800 LM
Material	Aluminum
Maximum Operating Temperature	25
media	Yes
Number of Lamps	1
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	3
Wattage	16

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	2700 ,3000 ,3500 ,4000 ,5000 ,Variable
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate
Style	CONTEMPORARY



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

Height	1.25
Length	6.69
Width	6.69

Descriptions

Construction	Canless,New Construction,Remodel
Description	6" LED WAFER 27K/3K/35K/4K/5K 800/1050/1300LM
extra long description	LITH WF6 ALO20 SWW5 90CRI CP6 MW M2
Features	Design Select
Long Description	The 6in Canless Wafer Downlight has an innovative, slim design that installs quickly and easily into as little as 3in of plenum space allowing for it to fit into ceiling spaces where most traditional recessed housings do not. Wafers install directly into dry wall eliminating the need for recessed housings. Once installed, our Wafer provides an all-in-one design featuring switchable white color temperature and adjustable lumen output technology. This technology gives the ultimate in flexibility, providing y
Product Type	Downlight

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00197589041248
Manufacturers Part Number	WF6 ALO20 SWW5 90CRI MW M6
UPC	197589041248

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
----------------------	--

Trade Size

aperture size	6 in
---------------	------

Packaging

Carton	1
Package	6
Weight	1.23
Weight Per each	1.36

Uses, Certifications, and Standards

Application	Decorative,Hospitality,Residential,Retail
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSAusCA Title 24,ENERGY STAR,FCC 47CFR Part 15 Consumer,JA8