ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WFD30LASPL Wi-Fi Smart Univ Dimmer, LT Almond

Eaton Wiring Devices

Catalog Number	WFD30LASPL
Manufacturer	Eaton Wiring Devices
Description	Eaton Wi-Fi Smart Dimmer Switch, Residential, Flush, 120V, Back and Side Wire, Light Almond, 60HZ, Single-Pole, Multi, Single-Gang, , 450W Dimmable Led/CFL, 600W Incandescent, Halogen, Magnetic Low Voltage, Electronic Low Voltage, Used With Wacd, Wifi
Weight per unit	0.3700 (lbs/each)
Product Category	Wiring Devices

Features

dimensions	2.2600 IN X 2.2600 IN X 6.4100 IN
Voltage Rating	120 V
Wattage	450 W (LED, CFL), 600 W (INC/HAL, ELV, MLV)

Descriptions

Description	WI-FI SMART UNIV DIMMER, LT ALMOND
extra long description	EWD WFD30-LA-SP-L Wi-Fi Smart Univ
Features	Wi-fi smart switches, receptacles, and dimmers from Eaton set up quickly and easily with Amazon's Alexa app–no other hubs or controllers are necessary. Plus Frustration Free Setup starts the connection automatically. Schedule lights to go on and off–and even dim–to fit your daily routine. Save energy and feel more comfortable and secure. You can even add voice-control using an Amazon Echo device.
Long Description	Eaton Wi-Fi smart dimmer switch,Residential,Flush,120V,Back and side wire,Light Almond,60Hz,Single-pole,Multi,Single-gang,,450W Dimmable LED/CFL,600W Incandescent,Halogen,Magnetic Low Voltage,Electronic Low Voltage,Used with WACD, WiFi
Product Type	Wi-Fi Smart Univ Dimmer, LT Almond

Manufacturer Information

Brand	Eaton
GTIN	00786689366858
Manufacturers Part Number	WFD30-LA-SP-L
UPC	786689366858

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer switch

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	36
Weight Per each	0.37

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Frequency Rating	60 Hz
Operating Temperature	32 to 104 °F (0 to 40 °C)
standard	NOM,cULus Listed,California Code of Regulations Title 24