



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF6ADJLED30K40KB 6" 13W Led Wafer Gimbal 3K/4K/5K Select BLK *Lithonia Lighting*

Catalog Number	WF6ADJLED30K40KB
Manufacturer	Lithonia Lighting
Description	6" Wafer-Thin Led Downlight, Adjustable, Round, Led, Switchable White, 90 Cri, Matte Black
Weight per unit	2.2 (lbs/each)
Product Category	Lighting

Features

dimnable	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1100 LM
Material	Aluminum
Maximum Operating Temperature	25
media	Yes
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	5
Wattage	14

Material, Color, and Finish

Color	Black
color rendering index (cri)	90
color temperature	Variable
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate

Dimensions and Weight

Height	1.7
Length	7
Width	7

Descriptions

Construction	Canless,New Construction,Remodel
Description	6" 13W LED WAFER GIMBAL 3K/4K/5K SELECT BLK
extra long description	LITH WF6 ADJ LED 30K40K50K 90CRI MB
Long Description	6" wafer-thin LED downlight, Adjustable, Round, LED, Switchable White, 90 CRI, Matte black
Product Type	Downlight



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00193047545624
Manufacturers Part Number	WF6 ADJ LED 30K40K50K 90CRI MB
UPC	193047545624

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Downlight

Trade Size

aperture size	6 in
---------------	------

Packaging

Carton	1
Weight	1.6
Weight Per each	2.2

Uses, Certifications, and Standards

Application	Education,Hospitality,House of Worship,Residential,Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSACA Title 24,ENERGY STAR,JA8