



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **WF6LED30K40K50K0 \*Discontinued\* 6" Led Wafer 30K40K50K BRZ** *Lithonia Lighting - Acuity*

Catalog Number	WF6LED30K40K50K0
Manufacturer	Lithonia Lighting - Acuity
Description	Lith WF6 Led 30K40K50K 90CRI Orb M6
Weight per unit	2.2 (lbs/each)
Product Category	Led Recessed Architectural & S

### Features

dimensions	1100 LM
dimnable	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1100 LM
Material	Aluminum
Maximum Operating Temperature	25
media	Yes
pallet quantity	180
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	5
Wattage	14

### Material, Color, and Finish

Color	Bronze
color rendering index (cri)	90
color temperature	Variable
Finish	Oil Rubbed
Lens Color	WHITE
Lens Material	Polycarbonate

### Dimensions and Weight

Height	1.1
Length	6.7
Width	6.7

### Descriptions

Construction	Canless,New Construction,Remodel
Description	*DISCONTINUED* 6" LED WAFER 30K40K50K BRZ
Long Description	LITH WF6 LED 30K40K50K 90CRI ORB M6
Product Type	Downlight



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00191848254257
Manufacturers Part Number	WF6 LED 30K40K50K 90CRI ORB M6
UPC	191848254257

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Downlight

## Trade Size

aperture size	6 in
---------------	------

## Availability

Manufacturer Status	Inactive
---------------------	----------

## Packaging

Carton	1
Weight	1.6
Weight Per each	2.2

## Uses, Certifications, and Standards

Application	Education,Hospitality,House of Worship,Residential,Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSACA Title 24,ENERGY STAR,JA8