



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WF8SWW590CRIMWM6 8" 20W Led Wafer 27K/3K/35K/4K/5K WHT 120V *Lithonia Lighting - Acuity*

| | |
|------------------|--|
| Catalog Number | WF8SWW590CRIMWM6 |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | The Wafer Led Downlights With Switchable White Technology Provides High-Quality Light Output and Efficiency and Features A Switch For Easy Color Temperature Adjustment, While Eliminating The Need For Recessed Housings. |
| Weight per unit | 2.3 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|---------------|
| average life | 50,000 |
| dimensions | 1600 LM |
| dimnable | Yes |
| Hardware | Yes |
| Lamp Included | Yes |
| Lamp Type | LED - Dynamic |
| lumens | 1600 LM |
| Material | Aluminum |
| Shape | Round |
| Voltage Rating | 120 |
| Warranty | 3 |
| Wattage | 19.1 |

Material, Color, and Finish

| | |
|-------------------|--|
| Color | White |
| color temperature | 2700 ,3000 ,3500 ,4000 ,5000 ,Variable |
| Finish | Matte |
| Lens Color | WHITE |
| Lens Material | Polycarbonate |

Dimensions and Weight

| | |
|--------|-----|
| Height | 1.1 |
| Length | 8.9 |
| Width | 8.9 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Construction | Canless, New Construction, Remodel |
| Description | 8" 20W LED WAFER 27K/3K/35K/4K/5K WHT 120V |
| extra long description | LITH WF8 SWW5 90CRI MW M6 8IN wafer |
| Long Description | The Wafer LED Downlights with Switchable White technology provides high-quality light output and efficiency and features a switch for easy color temperature adjustment, while eliminating the need for recessed housings. |
| Product Type | Trim |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | JUNO |
| GTIN | 00194994243915 |
| Manufacturers Part Number | WF8 SWW5 90CRI MW M6 |
| UPC | 194994243915 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type | Downlight |

Trade Size

| | |
|---------------|------|
| aperture size | 8 IN |
|---------------|------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 2.3 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Education, Healthcare, Hospitality, House of Worship, Residential, Retail, Sports and Recreation |
| environmental conditions | Indoor, Outdoor |
| Mounting | Recessed |
| standard | CSACA Title 24, ENERGY STAR, JA8 |