



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WFD30LASPL Wi-Fi Smart Univ Dimmer, LT Almond *Eaton Wiring Devices*

Catalog Number	WFD30LASPL
Manufacturer	Eaton Wiring Devices
Description	Eaton Wi-Fi Smart Dimmer Switch, Residential, Flush, 120V, Back and Side Wire, Light Almond, 60HZ, Single-Pole, Multi, Single-Gang, , 450W Dimmable Led/CFL, 600W Incandescent, Halogen, Magnetic Low Voltage, Electronic Low Voltage, Used With Wacd, Wifi
Weight per unit	0.3700 (lbs/each)
Product Category	Wiring Devices

Features

dimensions	2.2600 IN X 2.2600 IN X 6.4100 IN
Voltage Rating	120 V
Wattage	450 W (LED, CFL), 600 W (INC/HAL, ELV, MLV)

Descriptions

Description	WI-FI SMART UNIV DIMMER, LT ALMOND
extra long description	EWD WFD30-LA-SP-L Wi-Fi Smart Univ
Features	Wi-fi smart switches, receptacles, and dimmers from Eaton set up quickly and easily with Amazon's Alexa app--no other hubs or controllers are necessary. Plus Frustration Free Setup starts the connection automatically. Schedule lights to go on and off--and even dim--to fit your daily routine. Save energy and feel more comfortable and secure. You can even add voice-control using an Amazon Echo device.
Long Description	Eaton Wi-Fi smart dimmer switch,Residential,Flush,120V,Back and side wire,Light Almond,60Hz,Single-pole,Multi,Single-gang,,450W Dimmable LED/CFL,600W Incandescent,Halogen,Magnetic Low Voltage,Electronic Low Voltage,Used with WACD, WiFi
Product Type	Wi-Fi Smart Univ Dimmer, LT Almond

Manufacturer Information

Brand	Eaton
GTIN	00786689366858
Manufacturers Part Number	WFD30-LA-SP-L
UPC	786689366858

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	36
Weight Per each	0.37

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Frequency Rating	60 Hz
Operating Temperature	32 to 104 °F (0 to 40 °C)
standard	NOM,cULus Listed,California Code of Regulations Title 24