



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WNRL50WH Netatmo Tru-Universal Dimmer WH

Pass & Seymour/Legrand

Catalog Number	WNRL50WH
Manufacturer	Pass & Seymour/Legrand
Description	P&S WNRL50WH Netatmo Tru-Universal
Weight per unit	0.2500 (lbs/each)
Product Category	Wiring Devices

Features

actuator	Paddle
connection	Wired
Connection Type	Back Wire
Electrical Rating	120V 700W (ELV), 120V 450W (LED), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 8A (EFL), 120V 700W (Halogen), 120V 5A (Fan Control), 120V 700W (Incandescent), 120V 450W (CFL)
media	Yes
Mounting Type	Box
Number of Switches	1.0
Number of Wires	4.0
Poles	3-Way, Single Pole, Multi-Location
Voltage	120.0 V
Wattage	700

Material, Color, and Finish

Color	White
Finish	Matte

Descriptions

Description	NETATMO TRU-UNIVERSAL DIMMER WH
Features	Smart Lighting, With Netatmo
Long Description	P&S WNRL50WH NETATMO TRU-UNIVERSAL
Product Type	Netatmo Tru-Universal Dimmer, WH
Special Features	Incandescent, Halogen & ELV (FWD): 700W, MLV (FWD) : 500VA, LED/CFL/EFL (FWD): 450W / 3.8A, Incandescent, Halogen & ELV (REV): 450W, LED/CFL/EFL (REV): 250W / 2.1A

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007290080
Manufacturers Part Number	WNRL50WH
UPC	785007290080



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer

Packaging

Carton	1
Package	10
Weight Per each	0.25

Uses, Certifications, and Standards

standard	UL, CULUS, IC, FCC, ROHS
----------	--------------------------