



PRE-CONFIGURED HDMI 2-PORT STRAP, WHITE

WP1011-WH | [On-Q](#)

FEATURES & BENEFITS

Get the latest in HD with this pre-configured HDMI strap.



Includes two blank ports for use with any keystone insert.
In-wall HDMI connection.

SPECIFICATIONS

GENERAL INFO

Color: White
Connection Type: HDMI A
Type: Preconfigured Decorator Strap

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990
CSA Standard: Yes
UL Listing No: ANSI/UL 1863
UL Standard: Yes
UN SPSC: 39121704

DIMENSIONS

Depth (Metric): 3.2 cm
Depth (US): 1.25"
Height (Metric): 10.6 cm
Height (US): 4.19"
Width (Metric): 4.2 cm
Width (US): 1.65"

TECHNICAL INFORMATION

Jack Connectors: Copper Alloy, Gold over Nickel Plated 19 pin HDMI A Female

Material: High Impact Flame Retardant Plastic

Mounting: Wall Box

OhmValue: 2 ohms max

Receptacle Type: 19 Pin HDMI A Female

Number Of Receptacles: 1x HDMI, 2x Keystone Cutouts



PRE-CONFIGURED HDMI 2-PORT STRAP, WHITE

WP1011-WH | [On-Q](#)

FEATURES & BENEFITS

Get the latest in HD with this pre-configured HDMI strap.



Includes two blank ports for use with any keystone insert.
In-wall HDMI connection.

SPECIFICATIONS

GENERAL INFO

Color: White
Connection Type: HDMI A
Type: Preconfigured Decorator Strap

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990
CSA Standard: Yes
UL Listing No: ANSI/UL 1863
UL Standard: Yes
UN SPSC: 39121704

DIMENSIONS

Depth (Metric): 3.2 cm
Depth (US): 1.25"
Height (Metric): 10.6 cm
Height (US): 4.19"
Width (Metric): 4.2 cm
Width (US): 1.65"

TECHNICAL INFORMATION

Jack Connectors: Copper Alloy, Gold over Nickel Plated 19 pin HDMI A Female

Material: High Impact Flame Retardant Plastic

Mounting: Wall Box

OhmValue: 2 ohms max

Receptacle Type: 19 Pin HDMI A Female

Number Of Receptacles: 1x HDMI, 2x Keystone Cutouts