



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WP3475IV Cat 5E QC A/B Keystone Conn Iv (M10)

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | WP3475IV |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Keystone Insert, Structured Wiring Application, Ivory Color, 1 CT;10 PK Package Quantity, Easily Terminate All Four Pairs Using The Legrand Punch & Go Tool (AC3400);RJ45 Inserts Can Be Terminated With Any 110 Punchdown Tool Special Features, Eia/Tia 568A/B Standards Met, 0.04 LB Weight |
| Weight per unit | 0.0417 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|------------|---|
| connection | RJ45 Female |
| insulation | Electrical Insulation Resistance: 500 (@ 100 VDC) |

Material, Color, and Finish

| | |
|--------|----------------|
| Finish | Smooth plastic |
|--------|----------------|

Dimensions and Weight

| | |
|------|--|
| Size | 0.76 x 0.67 x 1.18 (19.30 x 16.9 x 30) |
|------|--|

Descriptions

| | |
|------------------------|--------------------------------------|
| Description | CAT 5E QC A/B KEYSTONE CONN IV (M10) |
| extra long description | OnQ WP3475IV CAT 5E QC A/B KEYSTONE |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | LEGRAND-ON-Q |
| GTIN | 00804428036678 |
| Manufacturers Part Number | WP3475-IV |
| UPC | 804428036678 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | Miscellaneous residential devices |
| Type | RJ45 Female Cat 5e Keystone Insert |

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 60 |
| Weight Per each | 0.0417 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Enclosure | Housing Material: High Impact Flame Retardant Plastic |
| environmental conditions | 0 to 93 (relative humidity, non-condensing) |
| Mounting | Keystone opening |
| standard | CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0 |
| Temperature Rating | 14 to 140 F (-10 to 60 C) |