



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WP3450BE Cat 5E RJ45 T568 A/B CNCTR BL (M20)

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | WP3450BE  |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | Keystone Connector, Snap-In Connection, 5 Category Level, Blue, 1.28 In Length, 0.64 In Width, 0.87 In Height, +14 °F Operating Temperature, +140 °F Operating Temperature, 0.04 LB |
| Weight per unit  | 0.0391 (lbs/each)   |
| Product Category | Outlets, Jacks, & Plates  |

### Features

|                |   |
|----------------|---|
| connection     | RJ45 Female                                       |
| Current Rating | 1.5 (@ 20 degrees C)                              |
| insulation     | Electrical Insulation Resistance: 500 (@ 100 VDC) |

### Material, Color, and Finish

|        |   |
|--------|---|
| Finish | Molded plastic chemically etched with diamond core finish |
|--------|---|

### Dimensions and Weight

|      |   |
|------|---|
| Size | 0.67 x 076 x 1.18 (17.02 x 19.30 x 29.97) |
|------|---|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | CAT 5E RJ45 T568 A/B CNCTR BL (M20) |
| extra long description | OnQ WP3450BE CAT 5E RJ45 T568 A/B C |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Legrand On-Q   |
| GTIN                      | 00804428024903 |
| Manufacturers Part Number | WP3450BE       |
| UPC                       | 804428024903   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
| Type                 | RJ45 Female Cat 5e Keystone Insert     |

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 20     |
| Package         | 120    |
| Weight Per each | 0.0391 |

### Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Residential  |
| environmental conditions | 0 to 93 (relative humidity, non-condensing)                      |
| Mounting                 | Keystone opening   |
| standard                 | CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0 |