



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WR1010 1/0 to 1/0 H Tap

Abb Installation Products, Inc

Catalog Number	WR1010
Manufacturer	Abb Installation Products, Inc
Description	Aluminum Wide Range H-Type Compression Connector Main: 1/0-4 Acsr, 2/0-4 STR., 1- 2 Sol., Tap: 1/0-4 Acsr, 2/0-4 STR., 1-2 Sol., Die: 0
Weight per unit	0.0850 (lbs/each)
Product Category	Pole Line & Distribution Hardw

Features

connection	Compression
insulation	None
Material	Aluminum
Number of Conductors	2
Wire Size	Main: 1/0 to #4 ACSR or 2/0 to #4 STR or #1 to #2 SOL AWG , Tap: 1/0 to #4 ACSR or 2/0 to #4 STR or #1 to #2 SOL AWG

Dimensions and Weight

Size	Length 1-3/4 inch
------	-------------------

Descriptions

Description	1/0 TO 1/0 H TAP
extra long description	ABB WR1010 AL HTYPE COMP CONN 1/0-4
Long Description	Aluminum Wide Range H-Type Compression Connector Main: 1/0-4 ACSR, 2/0-4 Str., 1- 2 Sol., Tap: 1/0-4 ACSR, 2/0-4 Str., 1-2 Sol., Die: 0
Product Type	Al Htype Comp Conn 1/0-4ASCR 2/0-4
Special Features	Made of 1350 Aluminum Alloy for high strength and high conductivity. Standard Compression tools and dies install all sizes - no special tools needed. Field-proven ribbed design enables excellent connector/conductor contact without distorting the conductor's shape. Fold-in tabs provide tab interlock as tool closes. Prefilled with oxide inhibitor held captive in the rib/connection area

Manufacturer Information

Brand	Blackburn Mechanical
GTIN	00783786107452
Manufacturers Part Number	WR1010
UPC	783786107452

Taxonomies, Classifications, and Categories

Category Description	T&B C TAP LUGS
Type	H-Type Compression Tap Connector



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	25
Package	250
Weight Per each	0.085

Uses, Certifications, and Standards

Application	For Combinations of Aluminum to Aluminum and Aluminum to Copper Conductors
environmental conditions	All Seasons / Conditions
Mounting	None
standard	RUS Accepted. Complies with ANSI C119.4 Specifications
Temperature Rating	up to 90 C