



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WR20TRI WR Dup Recp Tamp Res 20A/125V Iv

*Pass & Seymour/Legrand*

Catalog Number	WR20TRI
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant, Weather-Resistant Commercial Grade Receptacles, 20A, 125V
Weight per unit	0.2005 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Side wire
Dielectric Strength	Withstands 1500V minimum
indoor/outdoor	Outdoor
Number of Wires	3
Outlet Type	Tamper-Resistant, Commercial, Weather-Resistant, Outdoor
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Height	3.281
Width	1.130

### Descriptions

Description	WR DUP RECP TAMP RES 20A/125V IV
extra long description	P&S WR20TRI WR DUP RECP TAMP RES 20
Long Description	Tamper-Resistant, Weather-Resistant Commercial Grade Receptacles, 20A, 125V
Product Type	WR Dup Recp Tamp Res 20A/125V Iv
Special Features	Auto-ground clip assures positive ground. WR marking on face as required by UL Standard. Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations. Strap tabs wrap around face to prevent strap from separating from face and back body. Tri-drive brass terminal screws. Side wire capability. Heavy-duty, brass strap for added strength and ground conductivity. UV-resistant nylon face for longer life under adverse environmental conditions. Two drive screws anchor stra



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007242546
Manufacturers Part Number	WR20TRI
UPC	785007242546

## Taxonomies, Classifications, and Categories

Category Description	WEATHERPROOF BOXES & COVERS
Type	Outlet

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.2005

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	CULUS, UL498, CSA C22.2 No. 42