



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WRD159 #1 to #1 H Tap Connector

Nsi Industries

Catalog Number	WRD159
Manufacturer	Nsi Industries
Description	Dual Rated Wide Range Tap Connectors 6-1 Awg Dual Rated Wide Range Tap Connectors Are Used For Combinations Of Aluminum and Aluminum-Cooper Conductors. Standard Compression Tools and Dies Install In All Sizes. They Have Formable Ribs to Provide Broader Contact Area. Fold-In Tabs Provide Positive Tab Interlock As Tool Closes. Made From High Strength Aluminum Alloy. All Connectors Are Reversible. Rated 600 Volts.
Weight per unit	2.8 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Conductor Size	1 AWG - 6 AWG
Material	Aluminum
Tap Size	1 AWG - 6 AWG
Voltage Rating	600V
Warranty	1 YEAR

Material, Color, and Finish

Color	Aluminum
Finish	Aluminum



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	#1 TO #1 H TAP CONNECTOR
extra long description	NSI WRD159 Al Wide Range Connector
Features	Dual Rated Wide Range Tap Connectors 6-1 AWG Dual rated wide range tap connectors are used for combinations of aluminum and aluminum-cooper conductors. Standard compression tools and dies install in all sizes. They have formable ribs to provide broader contact area. Fold-in tabs provide positive tab interlock as tool closes. Made from high strength aluminum alloy. All connectors are reversible. Rated 600 Volts.
Long Description	Dual Rated Wide Range Tap Connectors 6-1 AWG Dual rated wide range tap connectors are used for combinations of aluminum and aluminum-cooper conductors. Standard compression tools and dies install in all sizes. They have formable ribs to provide broader contact area. Fold-in tabs provide positive tab interlock as tool closes. Made from high strength aluminum alloy. All connectors are reversible. Rated 600 Volts.
Product Type	Al Wide Range Connector #1-1 Awg
Special Features	A Groove-2 3 4 6 (ACSR)-1 2 3 4 6 (STR)-2 3 4 6 (SOL) - B Groove-2 3 4 6 (ACSR)-1 2 3 4 6 (STR)-2 3 4 6 (SOL)

Manufacturer Information

Brand	NSi
GTIN	00662381002785
Manufacturers Part Number	WRD159
UPC	662381002785

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Wide Range Tap Connectors

Packaging

Carton	1
Weight Per each	2.75

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
-------------	---